UNIVERSAL FILTRATION

FILTER VESSEL DATASHEET





Magnetic insert for Bag Filter

MAGNETIC INSERT FOR BAG FILTER

MAGNETIC INSERT BAG FILTER UNIT

FILTER VESSEL DATASHEET

Contents

Magnetic insert for Bag Filter How to order Page 1 Page 2

MAGNETIC INSERT FOR BAG FILTER

MAGNETIC INSERT BAG FILTER UNIT

UNIVERSAL FILTRATION

Universal Filtration



1

Magnetic insert for Bag Filter

MAGNETIC INSERT

Choice of high magnetic strength – 4000 and 9000 gauss for effective removal of iron particles in combination use with filter bag.

Magnetic strength are permanent and reusable.

Features

- Reliable system and easy to clean after use.
- Permanent magnetic strength
- Use together with holder to position at center of filter bag
- Users may have up to 3 magnetic insert per holder to maximize the effect if you have a lot of iron particle to remove

Specification

• Size:

All 4 sizes available -1, 2, 3, 4

- Magnetic Strength:
 4000 and 9000 gauss
- Magnet per holder:
 - 1, 2, 3
- Max Operating Temperature: 120 deg C

UNIVERSAL FILTRATION

Order Specification Code

Product Code	MI- 1 A 2 - 4000
No of magnet per holder 1, 2, 3	
Material A – SS304 S – SS316	
For Bag Size 1 - #1, 2 - #2 3 - #3, 4- #4	
Magnetic Strength 4000, 9000 gauss	

How To Order From US

Send us an inquiry, we will respond with a quote

Whether its for filter housing, filter bags, cartridges, or customisable solutions, we'll respond with a quotation for your needs. We ensure the highest quality finishes and consistency in our products. Email us your requirements and we'll get in touch.

Purchase order & agreement, and production

Once a purchase order is made and our payments terms are agreed to, we'll begin production of your order. Depending on the order, our lead time would vary between one week to four weeks. We'll keep you updated on the progress and status.

Completion, delivery, and sea freight

Once completed, we'll arrange a sea freight shipment to your specified location. We deliver internationally. Delivery by courier is also available. Clients can choose to arrange for self collection direct from our factories through a forwarder, if they would like to handle their own shipment.

For Inquiry contact us at Sales-Inquiry@universal-filtration.com

rsal Filti

© 2020 Universal Filtration Solutions Asia Pte Ltd. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this document concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Universal Filtration Solutions Asia Pte Ltd as to the effects of such use or the results to be obtained. Universal Filtration Solutions Asia Pte Ltd assumes no liability arising out of the use $b_{N|V}$ others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

For Inquiry contact us at Sales-Inquiry@universal-filtration.com

Asia Pacific Regional Office Universal Filtration Solutions Asia Pte Ltd 81 Ubi Ave 4, UB-ONE #06-28 Singapore 408830

TOP ENTRY BAG FILTER VESSEL

TOP ENTRY FILTRATION UNIT